




**WIDEX CONSUMER GUIDE TO DIGITAL HEARING INSTRUMENTS**



**100% Digital Hearing Aid Styles**



# Widex Fully Digital Hearing Aid Technology

*Widex offers a complete selection of 100% digital hearing instruments for all types of hearing losses, including the following:*

## widex mind<sup>™</sup>440 Ultimate Dual ISP Digital

### Ultimate Performance in Noise

Next generation Dual Integrated Signal Processing (Dual ISP) technology  
High Definition Locator Microphone  
Speech Enhancer  
TruSound Stabilizer  
TruSound AOC

### Ultimate Listening Comfort in Noise

Noise Reduction System  
Wind Noise Reduction  
TruSound Stabilizer  
Up to 5 Customized Listening Programs

### Ultimate Sound Quality

107 dB Extended Input Dynamic Range  
15 Channel Processing  
TruSound Compression  
Soft Sounds Are Audible, Loud Sounds Are Not Uncomfortable.

### Ultimate High Pitch Hearing

The unique Audibility Extender moves higher-pitched sounds that cannot be heard into lower-pitched regions of usable hearing. The algorithm offers a full range of adjustment so it may be fit precisely to more individuals.

### Ultimate Storage of Use Information

Sound Diary II Improves Fitting and Use of Hearing Aids

### Ultimate in Stopping Hearing Aid Whistling... Almost Everywhere

Multi-Directional Active Feedback Cancellation

### Ultimate Hearing of Soft and Distant Speech

0 dB HL compression threshold

### Ultimate in User-Friendliness

Zen relaxation program  
SmartSpeak (and SmartTone)  
Optional Remote Control and Volume Control

### Ultimate in Battery Life

### Excellent Telephone Coil Sensitivity

## widex mind<sup>™</sup>330 High Level Dual ISP Digital

### Exceptional Performance in Noise

Next generation Dual Integrated Signal Processing (Dual ISP)  
High Definition Locator Microphone

### Exceptional Listening Comfort in Noise

Noise Reduction System  
Wind Noise Reduction  
Up to 4 Customized Listening Programs

### Exceptional Sound Quality

107 dB Extended Input Dynamic Range  
10 Channel Processing  
Soft Sounds Are Audible, Loud Sounds Are Not Uncomfortable.

### Exceptional High Pitch Hearing

The unique Audibility Extender moves higher-pitched sounds that cannot be heard into lower-pitched regions of usable hearing.

### Exceptional Storage of Use Information

Sound Diary II Improves Fitting and Use Of Hearing Aids

### Exceptional in Stopping Hearing Aid Whistling... Almost Everywhere

Multi-Directional Active Feedback Cancellation

### Exceptional Hearing of Soft and Distant Speech

0 dB HL compression threshold

### Exceptional User-Friendliness

SmartSpeak (and SmartTone)  
Optional Remote Control and Volume Control

### Exceptional Battery Life

### Excellent Telephone Coil Sensitivity

## widex AIKIA<sup>™</sup> Mid-Level ISP Digital

### Outstanding Performance in Noise

Use of State-Of-The-Art Integrated Signal Processing (ISP)  
Aikia Locator Microphone\*

### Outstanding Listening Comfort in Noise

Noise Reduction System  
Wind Noise Reduction  
Up to 4 Customized Listening Programs

### Outstanding Sound Quality

107 dB Extended Input Dynamic Range  
10 Channel Processing  
Soft Sounds Are Audible  
Loud Sounds Are Not Uncomfortable

### Sound Diary I

Improves Fitting and Use Of Hearing Aids

### Outstanding in Stopping Hearing Aid Whistling ... Almost Everywhere

Multi-Directional Active Feedback Cancellation

### Outstanding Hearing of Soft and Distant Speech

0 dB HL compression threshold

### Outstanding Battery Life

### Excellent Telephone Coil Sensitivity

## widex Flash<sup>™</sup> Basic Level ISP Digital

### Excellent Performance in Noise

Use of Integrated Signal Processing (ISP)  
Flash Locator Microphone

### Excellent Listening Comfort in Noise

Noise Reduction System with Adjustments  
Wind Noise Reduction  
Up to 4 Customized Listening Programs

### Excellent Sound Quality

107 dB Extended Input Dynamic Range  
5 Channel Processing  
Soft Sounds Are Audible, Loud Sounds Are Not Uncomfortable

### Excellent Storage of Use Information

Sound Diary I Improves Fitting and Use of Hearing Aids

### Excellent in Stopping Hearing Aid Whistling... Almost Everywhere

Active Feedback Cancellation

### Excellent Hearing of Soft and Distant Speech

0 dB HL compression threshold

### Excellent Battery Life

### Excellent Telephone Coil Sensitivity

## widex real<sup>™</sup> Lower Cost ISP Digital

### Very Good Performance in Noise

Use of Integrated Signal Processing (ISP)  
REAL Locator Microphone

### Very Good Listening Comfort in Noise

Noise Reduction System  
Wind Noise Reduction  
Up to 3 Customized Listening Programs

### Very Good Sound Quality

107 dB Extended Input Dynamic Range  
3 Channel Processing  
Soft Sounds Are Audible, Loud Sounds Are Not Uncomfortable.

### No Hearing Aid Whistling in Almost All Listening Situations

Active Feedback Cancellation

### Very Good Hearing of Soft and Distant Speech

0 dB HL compression threshold

### Excellent Battery Life

### Excellent Telephone Coil Sensitivity



www.widexusa.com